



# TECHNIWATCH

swiss precision tools

## RUBBER BANDS

Sulfur and latex-free, with no degassing

### **NO MORE OXIDATION ON YOUR STORED PARTS, THANKS TO THESE RUBBER BANDS.**

Sulfur is an essential element for vulcanisation on old commercial rubber bands. Yet cannot be used on metal parts because of the oxidation it causes. Brass, pink gold and silver are for example materials with a strong reaction in the presence of these old rubber bands.


Our rubber bands have undergone numerous approval tests in our field.

Compliant with RoHS standards, as well as sulfur they are free from heavy metals, which are harmful to health.

Being latex free means that there are no allergy problems.

A colour code has been implemented to increase your productivity. If you have a bag of rubber bands with a mix of all the sizes, this colour system makes it very quick to select the right size.

Another advantage is that these rubber bands are highly robust, and do not dry out over time. Your consumption will be lower if you use them correctly.



### **Technical specifications:**

- The length is measured flat (half-circumference)

- 8 sizes:

- **20 mm / Violet / thin**
- **40 mm / Green / thin**
- **60 mm / Blue**
- **100 mm / Yellow**
- **150 mm / Red**
- **150 mm / Pink / Large**
- **200 mm / Black / Large**
- **250 mm / White / Large**

### **Size:**

From 20 to 250 mm

### **Weight:**

From 20 g to 1 kg per bag

### **References:**

H461000-20-VI (Bag of 1000 pcs)  
H461000-40-V (Bag of 1000 pcs)  
H461000-60-B (Bag of 1000 pcs)  
H461000-100-J (Bag of 1000 pcs)  
H461000-150-R (Bag of 1000 pcs)  
H461000-150-RL (Bag of 250 pcs)  
H461000-200-NL (Bag of 250 pcs)  
H461000-250-BL (Bag of 250 pcs)

### **Techniwatch SA**

Route de la Jaluse 5b,  
2400 Le Locle  
Tel : 032 926 19 46  
[www.techniwatch.ch](http://www.techniwatch.ch)

Discover our presentation videos on our YouTube channel « Techniwatch SA »  
Also accessible by scanning the following QR code





# TECHNIWATCH

swiss precision tools

## RUBBER BANDS

Product details

### RECOMMENDATIONS:

TECHNIWATCH rubber bands have an elasticity of up to 600 %.

Nonetheless, the size must be suitable for the dimensions of your packaging.

Also, make sure that your trays are free from sharp edges, or the rubber bands could break.



### Techniwatch SA

Route de la Jaluse 5b,  
2400 Le Locle  
Tel : 032 926 19 46  
[www.techniwatch.ch](http://www.techniwatch.ch)

Discover our presentation videos on our YouTube channel « Techniwatch SA »  
Also accessible by scanning the following QR code

